

Garant**Master Mute boring bar A.. STFCL 90°, for indexable inserts TC.., left****Order data**

Order number	265025 16/11
GTIN	4069515024914
Item class	29E

Description**Version:**

Round shank without clamping face.

Note:

Boring bar can be shortened as far as length L_{min} . Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Overhang L_1	96 mm
Minimum pre-drill $\varnothing D_{min}$	20 mm
Overall length L	158 mm
Setting angle κ	90 degrees
Shank $\varnothing D_s$	16 mm
ISO code toolholder	A16X STFCL/L11
Set of insert screws	269028 38
Standard	Works standard
Series	Master Mute
suitable indexable insert	TC.. 1102..
Centre offset L_3	11 mm
Insert size	11 mm
L_{min}	96 mm

Data sheet

Connection thread	G1/4
Application type	left-hand
Shank type	Steel
Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Application	Facing
Type of product	Boring Bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265025-16/11>