

**Self-levelling cross-hair laser GLL, Type: GLL20BOX****Order data**

Order number	468490 GLL20BOX
GTIN	4053423303339
Item class	46T

Description**Version:**

Green cross-hairs for optimum visibility even under poor lighting conditions. Thanks to the rubber-reinforced housing and IP65 protection class, the lasers are durable and suitable for robust use on construction sites. Convenient, quick and secure attachment thanks to the LB 10 professional universal holder with very strong magnets. Dual power supply enables seamless switching between Li-ion rechargeable battery and alkaline batteries, eliminating downtime. One horizontal and 2 vertical 360° lines permit a wide range of new applications for simultaneous marking, alignment and levelling indoors. Large working range up to 120 m using the LR 7 Professional receiver (accessories).

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

3.7V Li-Ion rechargeable battery, USB-C cable, LB 10 universal holder, laser target plate, bag and tradesman's case.

Technical description

Battery voltage	3.6 V
-----------------	-------

Data sheet

Weight	560 g
Colour of the laser	green
Laser class	2
Interface	Bluetooth® interface
IP Index of Protection	IP 65
Type of rechargeable battery	Lithium-ion
Length	129 mm
Range	20 m
Threaded socket for stand	1/4 in
Power supply	Battery-powered
Packaging	Carrying case
Number of rechargeable batteries contained	1
Width	68 mm
Height	116 mm
Series	GLL
Error limit	±0.3 mm/m
Levelling range	±4 degrees
Type of product	Cross laser