

Garant
Boring bar carbide, right-hand, Overhang / insert size: 100/06mm

Order data

Order number	268732 100/06
GTIN	4045197545862
Item class	21V

Technical description

suitable indexable insert	GCCT 06020.
Centre offset L_3	9.15 mm
Pack of insert screws	269028 11
Minimum pre-drill $\varnothing D_{\min}$	15.52 mm
ISO code toolholder	E12M SGLCR/L06
Insert size	6 mm
Overall length L	150 mm
Clamping height L_2	11.33 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7
Set of insert screws Type 11	269028 11
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200