

Garant
Boring bar carbide, left-hand, Overhang / insert size: 75/S5mm

Order data

Order number	268736 75/S5
GTIN	4045197545879
Item class	21V

Technical description

suitable indexable insert	GPCT S5010.
Insert size	5 mm
Minimum pre-drill $\varnothing D_{\min}$	9.15 mm
Centre offset L_3	5.6 mm
ISO code toolholder	E06J SGLPR/LS5
Pack of insert screws	269028 6
Overall length L	110 mm
Clamping height L_2	5.54 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	6 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Set of insert screws Type 6	269028 6
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500