



Impact wrench 12 V, cordless impact wrench, suitable for steels



Order data

Order number	074014 M12CIWF125
GTIN	4058546483265
Item class	03L

Description

Version:

- Robust and powerful FUEL™ cordless impact screwdriver with brushless POWERSTATE™ EC motor.
- Long motor service life and high energy efficiency.
- Sturdy metal gearbox casing and ergonomic central handle with soft-grip coating.
- Battery charge display.
- LED illumination of the working area.
- Reversible, with electronic speed control.
- REDLINK PLUS™ electronics – for unique power management.
- DRIVE CONTROL™ permits quick switching between the available settings with different speeds and torques.

With friction ring.

Supplied with:

Supplied with 2× Li-ion high-power batteries, charger, HD box.

Note:

See No. 073801 – 073840 for suitable batteries and chargers.

Technical description

Data sheet

Number of impacts 3rd stage	0 - 3300 min ⁻¹
Battery voltage	12 V
Tool arbor drive profile	External square drive
Type of rechargeable battery	Lithium-ion
Number of impacts 2nd stage	0 - 3000 min ⁻¹
maximum torque 1st step	542 Nm
maximum vibration to EN	1.5 m/s ²
Number of rechargeable batteries contained	2
Weight	1 kg
Packaging	Modular case (HD=Heavy Duty)
Manufacturer's designation	M12FCIWF12G3-502X
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
maximum screw Ø (8.8 - 12.9)	M16
typical application	Heavy Duty
Number of impacts 1st stage	0 - 1500 min ⁻¹
Power supply	Battery-powered
Battery capacity	5 Ah
Tool arbor size	1/2 in
Type of product	Impact wrench