

**Garant**
**Screw-on toolholder, left-hand, Shank / insert size: 16/11mm**

**Order data**

Order number	261109 16/11
GTIN	4045197655790
Item class	21T

**Technical description**

Functional width L <sub>4</sub>	20 mm
Pack of insert screws	269028 22
Shank size	16 mm
Head length L <sub>1</sub>	21.5 mm
suitable indexable insert	VB.. 1103..
Insert size	11 mm
ISO code toolholder	SVJBR/L 1616H11
Overall length L	100 mm
Series	QuickTurn
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500