

Garant**Master Mute exchangeable cutting head, right-hand, for CN.. indexable inserts****Order data**

Order number	265102 40/12
GTIN	4069515031769
Item class	29E

Description**Suitable for:**

Vibration-damping boring bar shanks No. 265060 – 265076.

Technical description

Centre offset L_3	27 mm
Insert size	12 mm
Lever screw	259018 18
Minimum pre-drill $\varnothing D_{\min}$	50 mm
suitable indexable insert	CN.. 1204..
Overall length L	26 mm
Lever	259015 18
Series	Master Mute

Shim	269005 13
Shank Ø D _s	40 mm
Number of coolant channels	3
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265102-40/12>