

Garant**Master Mute exchangeable cutting head, left-hand, for DN.. indexable inserts****Order data**

Order number	265115 32/11
GTIN	4069515031851
Item class	29E

Description**Suitable for:**

Vibration-damping boring bar shanks No. 265060 – 265076.

Technical description

Lever	259015 21
Overall length L	26 mm
Insert size	11 mm
Minimum pre-drill $\varnothing D_{\min}$	40 mm
Shim	269005 20
Lever screw	259018 19
suitable indexable insert	DN.. 1104..
Centre offset L_3	22 mm
Series	Master Mute

Data sheet

Shank Ø D _s	32 mm
Number of coolant channels	3
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265115-32/11>