

**Garant****Mini burr GARANT Master Uni – medium, Carbide, Type: C0210****Order data**

Order number	546906 C0210
GTIN	4069515032087
Item class	51D

**Description****Version:**

Carbide mini burr with shank  $\varnothing$  3 mm.

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Technical description**

Overall length	40 mm
Head length	10 mm
Shape description	ball nose
Head $\varnothing$	2 mm
Series	Master Uni
Shank $\varnothing$	3 mm
Tool material	Carbide
Long shank	no
Type of product	Burr

**User data**

	Suitability	$V_c$	ISO code
--	-------------	-------	----------

## Data sheet

Alu Mg	suitable only under restricted conditions
Steel < 900 N/mm <sup>2</sup>	suitable
Steel < 1400 N/mm <sup>2</sup>	suitable
Steel < 55 HRC	suitable
Steel < 60 HRC	suitable
INOX	suitable
Ti	suitable
GG(G)	suitable
Uni	suitable