

**Garant**

**Side lock arbor Form ADB with cooling channel bores, SK 40 A = 130,  
Clamping range Ø D1: 8mm**

**Order data**

Order number	300271 8
GTIN	4045197645913
Item class	31A

**Description****Version:**

With Balluff/RFID chip bore.

**GARANT –**

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

**With coolant supply holes that can be plugged.**

**Application:**

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

**Technical description**

Clamping Ø D <sub>1</sub>	8 mm
Overhang dimension A	130 mm
Spare clamping screw No. 30 9900	8
External Ø D	28 mm
Adapter	SK 40 A = 130
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	ADB

Cooling channel bore	pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HPC
Type of product	Side lock arbor

## Accessories

Pull studForm B suitable for steep tapers 40	308640 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull studsealed suitable for steep tapers 40	308660 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
	308740 40

Special pull stud with internal thread suitable for steep tapers 40

Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40

308820 40

Special pull stud with no internal thread sealed suitable for steep tapers 40

308700 40

Wrench for pull studs ISO 7388 suitable for ISO taper size 40

308830 40

Pull stud 45° sealed suitable for steep tapers 40

308765 40

Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40

308625 40

Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40

308630 40

Spare clamping screw for chucks with clamping Ø D1 8 mm

309900 8