

Working platforms for fork-lift trucks, Type: 1040X1200



Order data

Order number	919981 1040X1200
GTIN	4052462012004
Item class	94B

Description

Version:

Work platform in sturdy steel tube design made of round sections with all-round fall protection, including 2 PPE attachment fixtures. Rear wall of mesh and non-slip work platform. With a folding protective grille. Can be picked up transversely by a fork lift truck at the wide side. Insertion pins prevent the platform slipping off the forks. With galvanised tool storage tray. Rail height 1.10 m.

Application:

For safe working on repair and maintenance tasks on high parts of buildings, ceiling lights etc.

Standard:

TÜV approved, satisfies the DGUV (German statutory accident insurance) 208-031.

Colour:

Yellow orange RAL 2000 **painted.**

Note:

Please comply with national regulations regarding use of working platforms with the fork-lift truck. Suitable working platforms for use in Austria (approved by TÜV Austria) and Belgium are available on request.

Technical description

Data sheet

Depth	1040 mm
Weight	91 kg
Safe working load	300 kg
Footprint depth	800 mm
Fork insertion slots dimension A	200 mm
Width	1200 mm
Fork insertion slots dimension D	80 mm
Footprint width	1200 mm
Fork-lift fork socket pitch B	600 mm
Height	1990 mm
Pick-up by fork lift truck	Picked up transversely
Type of product	Work platform