

**Garant**
**Axial grooving insert, internal, right-hand, L1 = 15 mm, Ø Dmin / W: 6,2/3mm**

**Order data**

Order number	270360 6,2/3
GTIN	4045197467256
Item class	21I

**Description**
**Application:**

For cutter holder No. 270200 – 270204.

**Technical description**

Tip centre offset L <sub>3</sub>	2.95 mm
Minimum Ø D <sub>min</sub>	6.2 mm
Shank Ø d	6 mm
maximum cutting depth t <sub>max</sub>	6 mm
Radius R	0.1 mm
Overhang L <sub>1</sub>	15 mm
Product name attribute	L <sub>1</sub> = 15 mm
Type of product	Cutter insert for turning

**User data**

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable only under restricted conditions	250 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	200 m/min	N

Alu > 10% Si	suitable only under restricted conditions	200 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	160 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	150 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	150 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	60 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	30 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	90 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	60 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	30 m/min	S
GG(G)	suitable	90 m/min	K
CuZn	suitable	150 m/min	N
continuous	suitable		
irregular	suitable only under restricted conditions		
interrupted	suitable only under restricted conditions		
wet maximum	suitable		