

Working platforms for fork-lift trucks, Type: 1040X1305



Order data

Order number	919980 1040X1305
GTIN	4052462065697
Item class	94B

Description

Version:

Work platform in sturdy rectangular hollow section design for picking up transversely or longitudinally with a fork lift truck. Rear wall of mesh. Non-slip working platform and automatic door lock. Insertion slots with anti-slip protection (insertion pins). With two folding protective grilles with safety device, on the transverse and longitudinal sides. With galvanised tool storage tray and 2 PPE attachment fixtures. Rail height 1.10 m. Insertion slot distance B: 600 mm when picked up transversely, 190 mm when picked up longitudinally.

Application:

For safe working on repair and maintenance tasks on high parts of buildings, ceiling lights etc.

Standard:

TÜV approved, satisfies the DGUV (German statutory accident insurance) 208-031.

Colour:

Yellow orange RAL 2000 **painted.**

Note:

Please comply with national regulations regarding use of working platforms with the fork-lift truck. Suitable working platforms for use in Austria (approved by TÜV Austria) and Belgium are available on request.

Technical description

Data sheet

Width	1305 mm
Depth	1040 mm
Safe working load	300 kg
Fork-lift fork socket pitch B	600 mm
Fork-lift fork socket pitch B	190 mm
Footprint depth	800 mm
Footprint width	1200 mm
Fork insertion slots dimension D	80 mm
Height	2355 mm
Weight	139 kg
Fork insertion slots dimension A	200 mm
Pick-up by fork lift truck	Picked up transversely or longitudinally
Type of product	Work platform