



### , impact wrench, cordless impact wrench



#### Order data

|              |                |
|--------------|----------------|
| Order number | 070113 GSB1865 |
| GTIN         | 4053423321135  |
| Item class   | 03B            |

#### Description

##### Version:

**Bosch cordless hammer drill / driver** for very heavy-duty screwdriving, drilling and hammer drilling applications.

- **Electronic Cell Protection (ECP)** protects the battery against overheating and deep discharge.
- **Electronic Motor Protection (EMP)** protects the motor against overloading.
- **Mechanical multi-stage torque cut-out.**
- **Handy belt clip (not 070104).**
- **Integral LED light, battery charge indicator.**
- **Quick-clamping drill chuck.**

With **brushless EC motor.**

##### Supplied with:

**Without battery,** without charger and with L-BOXX.

##### Note:

Suitable replacement batteries and chargers can be found under No. 073851 – No 073866.

#### Technical description

|                       |       |
|-----------------------|-------|
| Suitable for material | Metal |
|-----------------------|-------|

## Data sheet

|                                                       |                            |
|-------------------------------------------------------|----------------------------|
| typical application                                   | Strong                     |
| Weight                                                | 1.1 kg                     |
| Motor design                                          | Brushless motor            |
| maximum torque soft                                   | 31 Nm                      |
| Packaging                                             | Modular case (L-Boxx)      |
| maximum hammer rate                                   | 27000 min <sup>-1</sup>    |
| Quick-clamping chuck range                            | 1.5 - 13 mm                |
| Power supply                                          | Battery-powered            |
| maximum twist drill size Ø in wood                    | 35 mm                      |
| maximum torque hard                                   | 65 Nm                      |
| maximum vibration to EN with hammer drill function    | 11 m/s <sup>2</sup>        |
| maximum speed 1st speed                               | 0 - 605 min <sup>-1</sup>  |
| Number of rechargeable batteries contained            | 0                          |
| Battery voltage                                       | 18 V                       |
| maximum speed 2nd speed                               | 2300 min <sup>-1</sup>     |
| Manufacturer's designation                            | GSB 18V-65                 |
| maximum twist drill size Ø in steel                   | 13 mm                      |
| Type of rechargeable battery                          | Lithium-ion                |
| maximum twist drill size Ø in concrete                | 13 mm                      |
| maximum vibration to EN without hammer drill function | 1.5 m/s <sup>2</sup>       |
| Type of product                                       | limpact drill /screwdriver |