



Combination face mill adapter, SK 50 A = 55, Spigot Ø d1: 27mm



Order data

Order number	302520 27
GTIN	4250122600831
Item class	36E

Description

Version:

Internal thread for manual clamping.

Application:

With drive key for milling cutters **with longitudinal groove**, e.g. DIN 841.

With face mill drive ring for milling cutters with **transverse slots**, DIN 1880.

Supplied with:

Drive key, face mill drive ring, and lock screw.

Optional extras:

Special toggle spanner No. 309840.

Technical description

Milling mandrel length L ₄	33 mm
Thread M	M24
Milling mandrel length L ₃ with drive ring	21 mm
Overhang dimension A	55 mm
Spare drive ring No. 309870	27
Overall length L	203 mm
Spigot Ø d ₁	27 mm
Suitable toggle spanner No. 309840	27
Spare milling cutter lock screw No. 309860 / 309861	27

Clamping Ø D ₁	27 mm
Adapter	SK 50 A = 55
Standard	DIN 6358
Arbor standard	DIN 2080
Concentricity	≤ 6 µm
Type of product	Milling cutter spigot

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/302520-27>