

Garant**GARANT Uni Hero solid carbide drill, plain shank DIN 6535 HB, TiAlSiN, Ø DC h7: 10,8mm****Order data**

Order number	123021 10,8
GTIN	4069515035064
Item class	13M

Description**Version:**

The ultimate in universality and profitability in one tool. **Robust tool design** and **convex-concave curved cutting edge design** for optimum tool stability and chip breakage in a wide range of materials. **Special chip chamber geometry** and **polished chip chambers** for ideal chip evacuation and maximum process reliability. **Ultra-smooth TiAlSiN high-performance coating** to effectively reduce wear and the formation of built-up edges.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

Feed f in steel < 1100 N/mm ²	0.21 mm/rev.
Flute length L_c	114 mm
recommended maximum drilling depth L_2	97.8 mm
Tolerance nominal Ø	h7
Number of cutting edges Z	2
Nominal Ø D_c	10.8 mm
Standard	Manufacturer's standard
Overall length L	162 mm
Shank Ø D_s	12 mm
Series	Uni

Data sheet

Coating	TiAlSiN
Tool material	Solid carbide
Version	4xD
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	orange
Type of product	Mono jobber drills

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions	140 m/min	N
Aluminium (short chipping)	suitable	150 m/min	N
Steel < 500 N/mm ²	suitable	120 m/min	P
Steel < 750 N/mm ²	suitable	115 m/min	P
Steel < 900 N/mm ²	suitable	110 m/min	P
Steel < 1100 N/mm ²	suitable	80 m/min	P
Steel < 1400 N/mm ²	suitable	70 m/min	P
INOX < 900 N/mm ²	suitable	65 m/min	M
INOX > 900 N/mm ²	suitable	60 m/min	M
Ti > 850 N/mm ²	suitable	35 m/min	S
GG(G)	suitable	95 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		

Air

suitable only under
restricted conditions