

**Garant**

**GARANT Uni Hero solid carbide drill, plain shank DIN 6535 HB, TiAlSiN, Ø DC h7: 4,2mm**



## Order data

|              |               |
|--------------|---------------|
| Order number | 122701 4,2    |
| GTIN         | 4069515033442 |
| Item class   | 13M           |

## Description

### Version:

**The ultimate in universality and profitability** in one tool. **Robust tool design** and **convex-concave curved cutting edge design** for optimum tool stability and chip breakage in a wide range of materials. **Special chip chamber geometry** and **polished chip chambers** for ideal chip evacuation and maximum process reliability. **Ultra-smooth TiAlSiN high-performance coating** to effectively reduce wear and the formation of built-up edges.

### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

## Technical description

|                                           |              |
|-------------------------------------------|--------------|
| Tolerance nominal Ø                       | h7           |
| Flute length $L_c$                        | 36 mm        |
| Shank Ø $D_s$                             | 6 mm         |
| Feed $f$ in steel $< 1100 \text{ N/mm}^2$ | 0.12 mm/rev. |
| Number of cutting edges $Z$               | 2            |
| recommended maximum drilling depth $L_2$  | 29.7 mm      |
| Nominal Ø $D_c$                           | 4.2 mm       |
| Overall length $L$                        | 74 mm        |
| Standard                                  | DIN 6537 L   |
| Series                                    | Uni          |

## Data sheet

|                    |                    |
|--------------------|--------------------|
| Coating            | TiAlSiN            |
| Tool material      | Solid carbide      |
| Version            | 4xD                |
| Point angle        | 140 degrees        |
| Shank              | DIN 6535 HB to h6  |
| Through-coolant    | yes                |
| Machining strategy | HPC                |
| Semi-Standard      | yes                |
| Colour ring        | orange             |
| Type of product    | Mono jobber drills |

## User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|-------------------------------------------|----------------|----------|
| Alu plastics                   | suitable only under restricted conditions | 190 m/min      | N        |
| Aluminium (short chipping)     | suitable                                  | 200 m/min      | N        |
| Steel < 500 N/mm <sup>2</sup>  | suitable                                  | 160 m/min      | P        |
| Steel < 750 N/mm <sup>2</sup>  | suitable                                  | 150 m/min      | P        |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  | 140 m/min      | P        |
| Steel < 1100 N/mm <sup>2</sup> | suitable                                  | 110 m/min      | P        |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  | 90 m/min       | P        |
| INOX < 900 N/mm <sup>2</sup>   | suitable only under restricted conditions | 90 m/min       | M        |
| INOX > 900 N/mm <sup>2</sup>   | suitable only under restricted conditions | 80 m/min       | M        |
| Ti > 850 N/mm <sup>2</sup>     | suitable                                  | 40 m/min       | S        |
| GG(G)                          | suitable                                  | 130 m/min      | K        |
| Uni                            | suitable                                  |                |          |
| wet maximum                    | suitable                                  |                |          |

Data sheet

|             |          |
|-------------|----------|
| wet minimum | suitable |
| Air         | suitable |