

Garant
Side lock arbor Form ADB, SK 40 A = 130, Clamping range Ø D1: 10mm

Order data

Order number	300270 10
GTIN	4045197283009
Item class	31A

Description
Version:

With Balluff/RFID chip bore.

GARANT –

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Overhang dimension A	130 mm
Clamping Ø D ₁	10 mm
Spare clamping screw No. 30 9900	10
External Ø D	35 mm
Adapter	SK 40 A = 130
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull studsealed suitable for steep tapers 40	308660 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull studForm A suitable for steep tapers 40	308600 40
	308630 40

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40

Pull stud 45°sealed suitable for steep tapers 40

308765 40

Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40

308801 40

Pull studsealed, form B suitable for steep tapers 40

308620 40

Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40

308615 40

Pull stud 60°sealed suitable for steep tapers 40

308785 40

Spare clamping screw for chucks with clamping Ø D1 10 mm

309900 10