

**Garant****Master Mute exchangeable cutting head, right-hand, for DC.. indexable inserts****Order data**

|              |               |
|--------------|---------------|
| Order number | 265218 40/11  |
| GTIN         | 4069515035583 |
| Item class   | 29E           |

**Description****Suitable for:**

Vibration-damping boring bar shanks No. 265060 – 265076.

**Technical description**

|                                          |             |
|------------------------------------------|-------------|
| Insert size                              | 11 mm       |
| Overall length L                         | 17 mm       |
| Insert screw                             | 269028 50   |
| Shim screw                               | 269013 8    |
| Minimum pre-drill $\varnothing D_{\min}$ | 50 mm       |
| Shim                                     | 269005 18   |
| suitable indexable insert                | DC.. 11T3.. |
| Series                                   | Master Mute |

|                              |              |
|------------------------------|--------------|
| Centre offset L <sub>3</sub> | 27 mm        |
| Shank Ø D <sub>s</sub>       | 40 mm        |
| Number of coolant channels   | 3            |
| Application type             | right-hand   |
| Through-coolant              | yes          |
| Type of product              | Cutting head |

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265218-40/11>