

Garant

**Side lock arbor Form ADB with cooling channel bores, SK 40 A = 130,
Clamping range \varnothing D1: 16mm**


Order data

| | |
|--------------|---------------|
| Order number | 300271 16 |
| GTIN | 4045197645951 |
| Item class | 31A |

Description
Version:

With Balluff/RFID chip bore.

GARANT –

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

With coolant supply holes that can be plugged.

Application:

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

| | |
|---------------------------------------|---------------|
| Spare clamping screw No. 30 9900 | 16 |
| Overhang dimension A | 130 mm |
| Clamping \varnothing D ₁ | 16 mm |
| External \varnothing D | 48 mm |
| Adapter | SK 40 A = 130 |
| Standard | DIN 6359 |
| Arbor standard | ISO 7388-1 |
| Shape | ADB |

| | |
|---------------------------------------|---------------------|
| Cooling channel bore | pluggable |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm |
| Concentricity | ≤ 3 μm |
| Machining strategy | HPC |
| Type of product | Side lock arbor |

Accessories

| | |
|---|------------|
| Pull stud 45°sealed suitable for steep tapers 40 | 308765 40 |
| Pull stud 90°sealed suitable for steep tapers 40 | 308795 40 |
| Pull studMori-Seiki, sealed, form A suitable for steep tapers 40 | 308625 40 |
| Pull studsealed, form B suitable for steep tapers 40 | 308650 40 |
| Pull stud, 18CrNiMo7Form A suitable for steep tapers 40 | 308605 40 |
| Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40 | 308801 40 |
| Special pull stud with no internal threadsealed suitable for steep tapers 40 | 308700 40 |
| Pull studsealed suitable for steep tapers 40 | 308660 40 |
| Pull stud 60°sealed suitable for steep tapers 40 | 308785 40 |
| Pull studForm A suitable for steep tapers 40 | 308600 40 |
| Pull studMori-Seiki, sealed, form A suitable for steep tapers 40 | 308630 40 |
| Pull stud Hurco 45° with fitsealed suitable for steep tapers 40 | 308802 40 |
| Pull studMazak, form A suitable for steep tapers 40M | 308670 40M |
| Pull stud 45°sealed suitable for steep tapers 40 | 308760 40 |
| Pull studsealed, form B suitable for steep tapers 40 | 308620 40 |
| Pull stud 90°sealed suitable for steep tapers 40 | 308790 40 |
| Special pull stud with internal thread suitable for steep tapers 40 | 308740 40 |

| | |
|---|-----------|
| Pull stud Hurco 90° with fitsealed suitable for steep tapers 40 | 308806 40 |
| Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40 | 308820 40 |
| Pull studsealed, form A suitable for steep tapers 40 | 308610 40 |
| Pull studsealed suitable for steep tapers 40 | 308635 40 |
| Pull studForm B suitable for steep tapers 40 | 308640 40 |
| Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40 | 308615 40 |
| Wrench for pull studsISO 7388 suitable for ISO taper size 40 | 308830 40 |
| Spare clamping screw for chucks with clamping Ø D1 16 mm | 309900 16 |