



Drill/driver, cordless drill/driver



Order data

Order number	075530 M18FHM121C
GTIN	4058546564339
Item class	03L

Description

Version:

- **Sturdy hammer drill with pneumatic hammer action**
- **High-strength metal gearbox casing.**
- **Forward / reverse, hammer action on / off and electronic speed control.**

M18 FUEL™ SDS-MAX cordless rotary hammer with brushless POWERSTATE™ motor. REDLINK PLUS™ electronics with new FORGE™ 12.0 Ah battery.

Supplied with:

Supplied with charger, 1× 18 V / 12 Ah FORGE™ battery, case

Note:

Suitable carbide hammer drills can be found from No. 787000.

See No. 073801 – No. 073840 for suitable batteries and chargers.

Technical description

Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Impact energy	11 J
Battery voltage	18 V

Data sheet

Power supply	Battery-powered
maximum twist drill size Ø in concrete	45 mm
Weight	10.2 kg
maximum hammer rate	2900 min ⁻¹
Manufacturer's designation	M18FHM-121C
maximum vibration to EN	9.4 m/s ²
Speed range	0 - 380 min ⁻¹
Battery capacity	12 Ah
Type of product	Hammer drill