



Wheel brush with shank waved, micro-abrasive, ceramic grit K320, Brush Ø D1× bristle width L1: 70X10mm



Order data

Order number	574462 70X10
GTIN	4017359672945
Item class	57L

Description

Version:

Abrasive nylon strands with silicon carbide, crimped into steel sleeve; **shank Ø 6 mm.**

Application:

For portable grinders, on flexible drive machines or drills for brushing surfaces. High speeds improve the brush performance.

Wet and dry fine rubbing down of aluminium, steel, stainless steel and plastics. Maximum operating temperature 80 °C.

Technical description

Shank Ø D _s	6 mm
Bristle width L ₁	10 mm
Length of brush section H ₁	20 mm
maximum speed	15000 min ⁻¹
Brush Ø D ₁	70 mm

Data sheet

recommended speed	4000 min ⁻¹
Grinding medium code	Ceramic
Type of product	Wheel brush