

**Garant**

**Side lock arbor Form ADB with cooling channel bores, SK 40 A = 130,  
Clamping range  $\varnothing$  D1: 18mm**


**Order data**

Order number	300271 18
GTIN	4045197645968
Item class	31A

**Description**
**Version:**

With Balluff/RFID chip bore.

**GARANT –**

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm

**With coolant supply holes that can be plugged.**

**Application:**

For clamping tools with side flat to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

**Technical description**

Spare clamping screw No. 30 9900	16
Overhang dimension A	130 mm
Clamping $\varnothing$ D <sub>1</sub>	18 mm
External $\varnothing$ D	50 mm
Adapter	SK 40 A = 130
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	ADB

Cooling channel bore	pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HPC
Type of product	Side lock arbor

## Accessories

Pull studsealed, form A suitable for steep tapers 40	308610 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull studForm A suitable for steep tapers 40	308600 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull studForm B suitable for steep tapers 40	308640 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
	308802 40

Pull stud Hurco 45° with fitsealed suitable for steep tapers  
40

Pull stud 60°sealed suitable for steep tapers 40

308785 40

Pull stud, 18CrNiMo7Form A suitable for steep tapers 40

308605 40

Pull studMori-Seiki, sealed, form A suitable for steep tapers  
40

308630 40

Pull studsealed suitable for steep tapers 40

308660 40

Wrench for pull studsISO 7388 suitable for ISO taper size 40

308830 40

Hurco 45° pull stud with 4-mm bore and fitsealed suitable  
for steep tapers 40

308801 40

Pull stud 90°sealed suitable for steep tapers 40

308795 40

Spare clamping screw for chucks with clamping  $\varnothing$  D1 16  
mm

309900 16