

**Garant****VB.T 110304, Grade: HU7310**

## Order data

Order number	261224 HU7310
GTIN	4045197696236
Item class	21G

## Description

VB.T 110304 HU7310 Grade: HU7310  
Chip breaker: AM  
Tolerance: G  
Cutting depth  $a_p$ : 0.1 - 4 mm  
Feed  $f$ : 0.05 - 0.5 mm/rev.  
Cutting speed  $v_c$  main application: 350 - 600 m/min

## Technical description

Cutting conditions	continuous
Cutting depth $a_p$	0.1 - 4 mm
Corner radius	0.4 mm
Feed $f$	0.05 - 0.5 mm/rev.
Main application	N
Chip breaker	AM

Cutting speed $v_c$ main application	350 - 600 m/min
Grade	HU7310
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
Coating	uncoated
ISO code indexable insert	VBGT 110304
Number of changes/inserts	2
Tolerance	G
Type of product	Indexable insert for turning