

**Hardness testing machine Rockwell, Type: HR-210****Order data**

Order number	495080 HR-210
GTIN	4550501372022
Item class	44F

Description**Version:**

Easy-to-use Rockwell hardness testing machine HR-210. The test force is applied by motor, reducing the operator's influence on the measurement. Analogue display. Manual weight change for overall test force.

Standard:

ISO 6508-2, JIS B 7726

Supplied with:

Flat anvil Ø 64 mm, Vee anvil Ø 40 × 30 mm, spirit level.

Optional extras:

Diamond penetration head incl. DAkkS calibration certificate No. 495092, power cable No. 495093, hardness comparison plates.

Technical description

Scale divisions	0.5 HR
Operation	manual
maximum sample width	165 mm

Data sheet

Display	Analogue dial indicator
Weight	69 kg
Height	1010 mm
Length	780 mm
maximum sample height	180 mm
Width	680 mm
Rockwell scales	A, B, C, D, E, F, G, H, K, L, M, P, R, S, V
Test procedure	Rockwell
Pre-load test force	98.07 N
Main load test force	588.4 N
Main load test force	980.7 N
Main load test force	1471 N
Standard	JIS B 7726
Standard	ISO 6508-2
Calibration	Price on request
Type of product	Hardness tester