

KÄRCHER

Industrial vacuum cleaner, Manufacturer's designation: IVRL65/12



Order data

Order number	078522 IVRL65/12
GTIN	4066529163899
Item class	07D

Description

Version:

Industrial vacuum cleaner suitable for vacuuming up and separating **coolants, lubricating emulsions, water or oil with solids (e.g. metal chips)**.

- **Compact design and robust materials for the best movement characteristics.**
- **Maximum flexibility in use and long working life for the oil-resistant power cable.**
- **Suction is applied via a 360° rotatable hose connection on the suction head.**

1-motor 1.2 kW industrial vacuum cleaner with **tilting mobility trolley** and **65 litre tank**.

Note:

A version with 100-litre stainless steel container can be found under No. 078522 size IVR-L100DP in our eShop.

Technical description

Dust class – vacuum cleaner	L
Dust class – vacuum cleaner	L
Height	1251 mm
Power consumption	1200 W

Data sheet

Number of turbines	1
Container volume	65 l
Connection width	DN50 mm
Vacuum	235 mbar
Weight	33 kg
Operating noise	70 dB(A)
Width	526 mm
Air flow volume	72 l/s
Length	718 mm
Type of product	Wet and dry vacuum cleaners