

KÄRCHER

Industrial vacuum cleaner, Manufacturer's designation: IVRL65/24



Order data

Order number	078522 IVRL65/24
GTIN	4066529164117
Item class	07D

Description

Version:

Industrial vacuum cleaner suitable for vacuuming up and separating **coolants, lubricating emulsions, water or oil with solids (e.g. metal chips)**.

- **Compact design and robust materials for the best movement characteristics.**
- **Maximum flexibility in use and long working life for the oil-resistant power cable.**
- **Suction is applied via a 360° rotatable hose connection on the suction head.**

2-motor 2.4 kW industrial vacuum cleaner with **tilting mobility trolley** and **65 litre tank**.

Note:

A version with 100-litre stainless steel container can be found under No. 078522 size IVR-L100DP in our eShop.

Technical description

Container volume	65 l
Connection width	DN50 mm
Vacuum	235 mbar
Air flow volume	144 l/s

Data sheet

Height	1326 mm
Power consumption	2400 W
Weight	43 kg
Width	532 mm
Cable length	6 m
Length	737 mm
Dust class – vacuum cleaner	L
Operating noise	70 dB(A)
Number of turbines	2
Type of product	Wet and dry vacuum cleaners