

Garant**VCMT indexable insert for finishing 30 pieces, HB7020-2, Size: 160404****Order data**

Order number	GG2865 160404
GTIN	4067263092278
Item class	GGN

Technical description

Main application	P
Cutting depth $a_{p \min}$	0.25 mm
Finishing/roughing assignment	Finishing
Tolerance	M
Number of changes/inserts	2
Cutting depth a_p	0.2 - 1.5 mm
Cutting depth $a_{p \max}$	2.5 mm
ISO code indexable insert	VCMT 160404
Tool material	Carbide
Contents	261372 HB7020-2
Corner radius	0.2 mm
Feed f	0.07 - 0.25 mm/rev.
Cutting speed v_c main application	140 - 400 mm/min
Quantity	30

Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2865 160404