

**VCMT indexable insert for finishing 30 pieces, HB7035-2, Size: 110302****Order data**

Order number	GG2866 110302
GTIN	4067263092278
Item class	GGN

Technical description

Contents	261364 HB7035-2
Main application	P
Cutting depth a_p	0.2 - 1.5 mm
Cutting depth $a_{p \max}$	1.75 mm
Number of changes/inserts	2
Cutting speed v_c main application	120 - 350 mm/min
Finishing/roughing assignment	Finishing
Corner radius	0.2 mm
Cutting depth $a_{p \min}$	0.15 mm
Tool material	Carbide
Tolerance	M
ISO code indexable insert	VCMT 110302
Feed f	0.07 - 0.25 mm/rev.
Quantity	30

Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2866 110302