

**Value pack CNMG indexable insert finishing 30 pieces HB7010-2****Order data**

Order number	GG2400 09T308
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.1 - 0.4 mm/rev.
ISO code indexable insert	CNMG 09T308
Tool material	Carbide
Corner radius	0.8 mm
Contents	250052 HB7010-2
Cutting speed v_c main application	170 - 500 mm/min
Finishing/roughing assignment	Finishing
Number of changes/inserts	4
Cutting depth $a_{p \min}$	0.55 mm
Cutting depth a_p	0.3 - 2 mm
Cutting depth $a_{p \max}$	3.25 mm
Main application	P
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2400 09T308
