

**DNMG indexable insert for medium machining 50 pieces, HB7035-2, Size: 110404****Order data**

Order number	GG2430 110404
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	DNMG 150608
Cutting depth $a_{p \min}$	0.25 mm
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.3 - 4 mm
Cutting depth $a_{p \max}$	2.75 mm
Number of changes/inserts	4
Main application	P
Tool material	Carbide
Contents	250752 HB7035-2
Corner radius	0.4 mm
Cutting speed v_c main application	120 - 320 mm/min
Feed f	0.2 - 0.5 mm/rev.
Quantity	50
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2430 110404
