



Value pack TNMG indexable insert finishing 30 pieces HBT020

Order data

Order number	GG3920 160404
GTIN	4067263093435
Item class	GGN

Technical description

ISO code indexable insert	TNMG 160404
Tool material	Carbide
Coating	TiCN
Main application	P
Number of changes/inserts	6
Feed f	0.1 - 0.45 mm/rev.
Corner radius	0.4 mm
Cutting depth a_p	0.8 - 5 mm
Cutting depth $a_{p \max}$	4 mm
Cutting depth $a_{p \min}$	0.25 mm
Cutting speed v_c main application	100 - 280 mm/min
Contents	251564 HBT020
Finishing/roughing assignment	Finishing
Quantity	30
Type	HBT020
Cutting conditions	slightly interrupted
Chip breaker	PM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3920 160404
