

**DNMG indexable insert for medium machining 50 pieces, HB7035-2, Size: 110408****Order data**

Order number	GG2430 110408
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	DNMG 110408
Cutting depth a_p	0.3 - 4 mm
Tool material	Carbide
Cutting depth $a_{p \min}$	0.55 mm
Finishing/roughing assignment	Finishing
Contents	250754 HB7035-2
Cutting depth $a_{p \max}$	2.75 mm
Main application	P
Corner radius	0.8 mm
Feed f	0.2 - 0.5 mm/rev.
Cutting speed v_c main application	120 - 320 mm/min
Number of changes/inserts	4
Quantity	50
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2430 110408
