



TNMG indexable insert for medium machining 50 pieces, HBT020, Size: 160404

Order data

Order number	GG3921 160404
GTIN	4067263093442
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	4 mm
Feed f	0.1 - 0.45 mm/rev.
Finishing/roughing assignment	Finishing
ISO code indexable insert	TNMG 160404
Contents	251564 HBT020
Number of changes/inserts	6
Cutting depth $a_{p \min}$	0.25 mm
Main application	P
Coating	TiCN
Cutting speed v_c main application	100 - 280 mm/min
Cutting depth a_p	0.8 - 5 mm
Corner radius	0.4 mm
Tool material	Carbide
Quantity	50
Type	HBT020
Cutting conditions	slightly interrupted
Chip breaker	PM

Type of product

Indexable insert for turning

Suitable products

No Shop URL available for: GG3921 160404
