

Garant**WNMG indexable insert for medium machining 30 pieces, HB7130-2, Size: 080404****Order data**

Order number	GG2983 080404
GTIN	4067263094937
Item class	GGN

Technical description

Cutting speed v_c main application	70 - 240 mm/min
Finishing/roughing assignment	Finishing
Quantity	30
Coating	coated
Cutting depth $a_{p \max}$	2.75 mm
Cutting depth $a_{p \min}$	0.8 mm
Feed f	0.1 - 0.5 mm/rev.
Cutting depth a_p	0.5 - 4 mm
Main application	M
Tolerance	M
Tool material	Carbide
Number of changes/inserts	6
Contents	252068 HB7130-2
Corner radius	0.4 mm

Data sheet

ISO code indexable insert	WNMG 080404
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2983 080404