

Garant**WNMG indexable insert for medium machining 30 pieces, HB7130-2, Size: 080412****Order data**

Order number	GG2983 080412
GTIN	4067263094975
Item class	GGN

Technical description

Quantity	30
Cutting speed v_c main application	70 - 240 mm/min
Contents	252072 HB7130-2
Corner radius	1.2 mm
Cutting depth $a_{p \max}$	2.75 mm
Cutting depth a_p	0.5 - 4 mm
ISO code indexable insert	WNMG 080412
Tool material	Carbide
Cutting depth $a_{p \min}$	0.8 mm
Finishing/roughing assignment	Finishing
Main application	M
Tolerance	M
Number of changes/inserts	6
Feed f	0.1 - 0.5 mm/rev.

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2983 080412