

Garant**VCMT indexable insert for medium machining 50 pieces, HB7035-2, Size: 110304****Order data**

Order number	GG2875 110304
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	80 - 290 mm/min
Number of changes/inserts	2
Main application	P
Cutting depth a_p	0.3 - 2 mm
Cutting depth $a_{p \max}$	1.75 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
Contents	261454 HB7035-2
Tolerance	M
Cutting depth $a_{p \min}$	0.25 mm
Quantity	50
Feed f	0.08 - 0.3 mm/rev.

Corner radius	0.4 mm
ISO code indexable insert	VCMT 110304
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2875 110304