

**VCMT indexable insert for medium machining 50 pieces, HB7035-2, Size: 160408****Order data**

|              |               |
|--------------|---------------|
| Order number | GG2875 160408 |
| GTIN         | 4067263092278 |
| Item class   | GGN           |

**Technical description**

|                                      |                    |
|--------------------------------------|--------------------|
| Contents                             | 261459 HB7035-2    |
| Tool material                        | Carbide            |
| Cutting depth $a_p$                  | 0.3 - 2 mm         |
| Feed $f$                             | 0.08 - 0.3 mm/rev. |
| Finishing/roughing assignment        | Finishing          |
| ISO code indexable insert            | VCMT 160408        |
| Quantity                             | 50                 |
| Corner radius                        | 0.8 mm             |
| Cutting depth $a_{p \max}$           | 2.5 mm             |
| Tolerance                            | M                  |
| Number of changes/inserts            | 2                  |
| Cutting speed $v_c$ main application | 80 - 290 mm/min    |

## Data sheet

|                            |                              |
|----------------------------|------------------------------|
| Cutting depth $a_{p \min}$ | 0.55 mm                      |
| Main application           | P                            |
| Type                       | HB7035-2                     |
| Cutting conditions         | heavily interrupted          |
| Chip breaker               | SM                           |
| Type of product            | Indexable insert for turning |

### Suitable products

No Shop URL available for: GG2875 160408