

Garant**VBMT indexable insert for medium machining 30 pieces, HB7140-2, Size: 160404****Order data**

Order number	GG3560 160404
GTIN	4067263092278
Item class	GGN

Technical description

Coating	coated
Cutting depth $a_{p \min}$	0.25 mm
Feed f	0.1 - 0.4 mm/rev.
Cutting depth a_p	0.5 - 2.5 mm
Finishing/roughing assignment	Finishing
Contents	261232 HB7140-2
Cutting depth $a_{p \max}$	2.5 mm
Corner radius	0.4 mm
Tool material	Carbide
Number of changes/inserts	2
Main application	M
ISO code indexable insert	VBMT 160404
Cutting speed v_c main application	60 - 200 mm/min

Data sheet

Tolerance	M
Quantity	30
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3560 160404