

Garant**GARANT INOX solid carbide milling cutter HPC, AlTiN, Ø e8 DC: 2mm****Order data**

Order number	202952 2
GTIN	4069515039529
Item class	11Z

Description**Version:**

Milling cutter with **optimised geometry** and modern **high-performance coating** for optimum metal removal rate in various **stainless steels**. Can also be used in **duplex materials**.

Dimensions similar to DIN 6527.

Advantage:

Particularly low vibration running.

Note:

Successor product to 202989.

Technical description

Shank	DIN 6535 HA to h6
Shank form	HA
Shank Ø D _s	6 mm
No. of teeth Z	4
Overhang length L ₁ incl. recess	8 mm
Feed f _z for slot milling in stainless steel > 900 N/mm ²	0.017 mm
Overall length L	57 mm
Tolerance nominal Ø	e8
Cutting edge Ø D _c	2 mm
Flute length L _c	5 mm

Data sheet

Recess Ø D ₁	1.8 mm
Helix angle	40 degrees
Corner rounding r _v	0.1 mm
Direction of infeed	horizontal, oblique and vertical
Feed f _z for side milling in INOX > 900 N/mm ²	0.024 mm
Coating	AlTiN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Spacing of the cutters	unequal spacing
Cutting width a _e for milling operation	0.3×D for side milling
Cutting width a _e for milling operation	0.3×D for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	blue
Type of product	End / face mill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable only under restricted conditions	240 m/min	P
Steel < 750 N/mm ²	suitable only under restricted conditions	220 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	200 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	180 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	150 m/min	P
TOOLOX 33	suitable only under restricted conditions	115 m/min	H

Data sheet

TOOLOX 44	suitable only under restricted conditions	80 m/min	H
INOX < 900 N/mm ²	suitable	100 m/min	M
INOX > 900 N/mm ²	suitable	90 m/min	M
wet maximum	suitable		
wet minimum	suitable		
dry	suitable only under restricted conditions		
Air	suitable		