

**CNMG indexable insert for finishing 50 pieces, HB7020-2, Size: 120408****Order data**

Order number	GG2405 120408
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	160 - 400 mm/min
Corner radius	0.8 mm
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	4.25 mm
Tool material	Carbide
Contents	250060 HB7020-2
ISO code indexable insert	CNMG 120408
Feed f	0.1 - 0.4 mm/rev.
Main application	P
Number of changes/inserts	4
Cutting depth a_p	0.3 - 2 mm
Cutting depth $a_{p \min}$	0.55 mm
Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2405 120408
