

Garant**Softcut® shoulder mill with bore, for indexable inserts AO..****Order data**

Order number	215411 40/4
GTIN	4069515038874
Item class	21O

Description**Version:**

High precision square shoulder mill with irregular pitch for very smooth cutting, very high precision and cutting power. **With special geometry for reduced cutting forces for MTC applications** under **unstable conditions** or for spindles with low drive power.

Application:

For shoulder milling in large depths, also slotting. General use in all steel materials as well as stainless and acid-resistant steels.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 1.5** with bit No. **674252 size 8IP**.

Technical description

$\varnothing D_3$	28.8 mm
Ramping length L for $\alpha_{\max}$	9.5 mm
Cutting edge $\varnothing D_c$	40 mm
suitable indexable insert	AO.T1104
Circular interpolation milling $\varnothing D_{\min}$	68.8 mm

Data sheet

Series	Softcut®
Mounting bore Ø	16 mm
Circular interpolation milling Ø D _{max}	77.3 mm
Ramping angle α _{max}	1.8 degrees
Overall length L _{tot}	40 mm
Circular interpolation milling a _p	3.4 mm
Number of cutting edges Z	4
Set of insert screws	219799 10 (8IP; 1.5 Nm)
Shank type	with bore
Setting angle κ	90 degrees
Milling application	Ramping
Milling application	Ramping
Milling application	Circular milling
Milling application	Plunging
Spacing of the cutters	unequal spacing
Through-coolant	yes
Machining strategy	MTC
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	Indexable end mill

Suitable products

No Shop URL available for: 215411 40/4