

Garant**VBMT indexable insert for medium machining 50 pieces, HB7130-2, Size: 160404****Order data**

Order number	GG3562 160404
GTIN	4067263097020
Item class	GGN

Technical description

Contents	261232 HB7130-2
Tool material	Carbide
Cutting depth a_p	0.5 - 2.5 mm
ISO code indexable insert	VBMT 160404
Main application	M
Finishing/roughing assignment	Finishing
Number of changes/inserts	2
Tolerance	M
Cutting depth $a_{p \max}$	2.5 mm
Cutting speed v_c main application	70 - 240 mm/min
Quantity	50
Cutting depth $a_{p \min}$	0.25 mm
Feed f	0.1 - 0.4 mm/rev.

Corner radius	0.4 mm
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3562 160404