

**CNMG indexable insert for finishing 50 pieces, HB7035-2, Size: 09T304****Order data**

Order number	GG2406 09T304
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Feed f	0.1 - 0.4 mm/rev.
Number of changes/inserts	4
Cutting depth $a_{p \min}$	0.25 mm
Corner radius	0.4 mm
ISO code indexable insert	CNMG 09T304
Contents	250050 HB7035-2
Cutting depth $a_{p \max}$	3.25 mm
Main application	P
Tool material	Carbide
Cutting speed v_c main application	150 - 350 mm/min
Cutting depth a_p	0.3 - 2 mm
Quantity	50
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2406 09T304
