

Garant**WNMG indexable insert for roughing 50 pieces, HB7130-2, Size: 080408****Order data**

Order number	GG2993 080408
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	60 - 220 mm/min
Finishing/roughing assignment	Roughing
ISO code indexable insert	WNMG 080408
Cutting depth a_p	1.5 - 6 mm
Corner radius	0.8 mm
Number of changes/inserts	6
Quantity	50
Cutting depth $a_{p \min}$	0.55 mm
Feed f	0.25 - 0.6 mm/rev.
Tool material	Carbide
Cutting depth $a_{p \max}$	2.75 mm
Main application	M
Contents	252208 HB7130-2
Type	HB7130-2

Cutting conditions	slightly interrupted
Chip breaker	VG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2993 080408