

Garant**VBMT indexable insert for medium machining 50 pieces, HB7140-2, Size: 160408****Order data**

Order number	GG3563 160408
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	VBMT 160408
Finishing/roughing assignment	Finishing
Tolerance	M
Cutting depth $a_{p \min}$	0.55 mm
Main application	M
Number of changes/inserts	2
Quantity	50
Corner radius	0.8 mm
Cutting depth $a_{p \max}$	2.5 mm
Cutting speed v_c main application	60 - 200 mm/min
Feed f	0.1 - 0.4 mm/rev.
Cutting depth a_p	0.5 - 2.5 mm
Tool material	Carbide

Contents	261234 HB7140-2
Coating	coated
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3563 160408