



Mechanic's side cutter chrome-plated with grips, overall length: 125mm



Order data

Order number	724201 125
GTIN	4003773005315
Item class	73F

Description

Version:

With slim head and induction hardened cutting edges. Cutter edge hardness approx. 63 HRC. Flush fitting joint with no play.

Pliers chrome-plated, handles with multi-component covers and KNIPEXtend interface.

Standard:

DIN ISO 5749

Material:

Special tool steel, drop-forged and oil-hardened.

Technical description

Cutting capacity soft wire up to Ø	2.5 mm
Cutting capacity piano wire up to Ø	0.6 mm
with return spring	no
Cutting capacity hard wire up to Ø	1 mm
with selectable return spring	no
overall length	125 mm
Standard	DIN ISO 5749
Handle	Multi-component covering

Data sheet

Manufacturing process	Cutting edges induction hardened (approx. 63 HRC)
Material	Special tool steel, drop-forged and oil-hardened
Surface	chrome-plated
Type of product	Cutting pliers