



RCK STG 10/800 control unit, Type: STG10/800



Order data

Order number	078146 STG10/800
GTIN	4007220523551
Item class	07P

Description

Version:

The RCK drive system with continuous speed control is an innovative solution that combines maximum productivity with significant ergonomic advantages. The system generates less noise and vibration than conventional drives. In combination with the mobile control unit and various hand-pieces, the system is particularly light, convenient and flexible for users when in use. In addition, the hand-pieces enable the use of a wide variety of tools in almost all industries. The system is designed for continuous use at a constant speed and, in addition to the power supply unit, can also be used with a powerful rechargeable battery.

Control unit that enables precise control of various hand-pieces. Achieves a maximum speed of 80,000 RPM and keeps it stable when in use.

Advantage:

- **Increases productivity by up to 50% thanks to constant speed.**
- **Comfortable, ergonomic working with fast, optimum results.**
- **Can be used with power supply unit or with rechargeable battery for mobile use, for a wide range of industrial applications.**

Technical description

Power consumption	1560 W
-------------------	--------

Weight	3.3 kg
--------	--------