

Garant**ER clamping nut High Speed, for ER: 11****Order data**

Order number	309595 11
GTIN	4069515040624
Item class	31Z

Description**Version:**

Thread and taper ground in a single setup for highest concentricity.

Nut coated for: lower friction and **increased clamping force** coupled with high wear resistance and corrosion resistance. **With hexagon** 17 AF.

Suitable for:

All standard ER collet chucks.

Optional extras:

ER clamping wrenches, No. 309680 – 309740.

Single open ended spanner (for size 16), No. 613300 size 25.

Note:

Collet chuck and clamping nut are balanced separately!

Technical description

Thread	M14x0.75
Overall length L	12 mm
External Ø D	19 mm
maximum tightening torque	40 Nm

Data sheet

Standard	DIN 6499 D
Type of product	Clamping nut