

**Value pack SNMG indexable insert medium machining 30 pieces HB7020-2****Order data**

Order number	GG2447 120408
GTIN	4067263093091
Item class	GGN

Technical description

ISO code indexable insert	SNMG 120408
Tool material	Carbide
Cutting depth a_p	0.3 - 4 mm
Cutting depth $a_{p \min}$	0.55 mm
Feed f	0.2 - 0.5 mm/rev.
Cutting speed v_c main application	130 - 370 mm/min
Main application	P
Cutting depth $a_{p \max}$	4.25 mm
Contents	251224 HB7020-2
Corner radius	0.8 mm
Number of changes/inserts	8
Finishing/roughing assignment	Finishing
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2447 120408
